

HITEMP140-TSK

HITEMP140 DATA LOGGER WITH THERMAL SHIELD



Features

- Withstands Temperatures between -200°C up to 250°C
- Small Diameter - 2.0" (51mm)
- Submersible
- Immediate or Delay Start
- Up to 1 Second Reading Rate

Benefits

- Validate a Wide Range of Temperature Processes Using One Data Logger
- HiTemp140 can be used With or Without Thermal Shield
- Durable Thermal Shield Protects Probe and Allows for a Fast Response Time

Applications

- Peanut Roasting
- Food Processing
- Meat Processing
- Autoclave Validation
- Conveyer Ovens
- Dishwasher Testing
- Incubator Validation

The HiTemp140-TSK is a kit that includes a HiTemp140 data logger housed in a thermal shield. The combined features of the $\pm 0.1\%$ accuracy of the HiTemp140 and the properties of the durable thermal shield allow the device to be used for a wide range of validation applications. This rugged system can be placed in and withstand temperature from -200°C to 250°C, making it ideal for use in autoclave validation, monitoring food processing and dishwasher testing.



Vented

Flush


Using the MadgeTech software, the data logger is fast and easy to setup. Remove the thermal shield and place the HiTemp140 into the IFC400 docking station (sold separately). Using the software, an immediate or delay start can be chosen, as well as the reading rate. Select Start to program the settings and start the data logger. Place the thermal shield around the HiTemp140 and screw it back together. The device is ready to be deployed.

The HiTemp140-TSK can be completely submerged and is built for applications that require extreme temperature monitoring.

MADGETECH DATA LOGGER SOFTWARE

Key

- A** Graph View
- B** Tabular Data View
- C** Statistics
- D** Digital Calibration
- E** Copy to Excel®



Software Features:

- Multiple graph overlay
- Statistics
- Digital calibration
- Zoom in/ zoom out
- Lethality equations (F_0 , PU)
- Mean Kinetic Temperature
- Full time zone support
- Data annotation
- Min./Max./Average lines
- Data table view
- Automatic report generation
- Summary view
- Multilingual

HITEMP140 SPECIFICATIONS (DATA LOGGER)*

Probe Measurement Range: -200°C to +260°C (-328°F to +500°F)

Temperature Resolution: 0.01°C (0.02°F)

Calibrated Accuracy: ±0.1°C/±0.18°F
(20°C to +140°C/68°F to +284°F)
±0.3°C/±0.54°F
(-20°C to +19.99°C/-4°F to +67.98°F)
±0.4°C/±0.72°F
(-40°C to -20.01°C/-40°F to -4.02°F)

Start Modes: Software programmable immediate start
Delay start up to 18 months in advance

Stop Modes: Manual or Timed (specific date and time)

Real Time Recording: May be used with PC to monitor and record data in real time

Password Protection: An optional password may be programmed into the device to restrict access to configuration options. Data may be read out without the password.

Memory: 32,700 readings

Wrap Around: Yes

Reading Rate: 1 second up to once every 24 hours

Battery Type: 3.6V high-temperature lithium battery included; user replaceable

Battery Life: 1 year typical (1 minute reading rate at 25°C/77°F)

Calibration: Digital calibration through software

Calibration Date: Automatically recorded within device

Data Format: Date and time stamped °C, °F, K, °R

Time Accuracy: ±1 minute/month at 20°C to 30°C (68°F to 86°F)

Computer IFC400 docking station required; 125,000 baud Interface:

Software: XP SP3/Vista/Windows 7/Windows 8

Operating Environment: -40°C to +140°C (-40°F to +284°F), 0%RH to 100%RH

Dimensions (Body): 1.9" x 0.970" dia. (48mm x 24.6mm dia.)

Model Number: Dimensions (Probe)

HITEMP140-2 2.0" x 0.188" dia. (51mm x 4.8mm dia.)
HITEMP140-2-TD 2.0" x 0.125" dia. (0.188" transitional dia.)
51mm x 3.2mm dia. (4.8mm transitional dia.)

HITEMP40-5.25 5.25" x 0.188" dia. (133mm x 4.8mm dia.)
HITEMP140-5.25-TD 5.25" x 0.125" dia. (0.188" transitional dia.)
133mm x 3.2mm dia. (4.8mm transitional dia.)

HITEMP140-7 7.0" x 0.188" dia. (178mm x 4.8mm dia.)

Weight: 4.2 oz (120g)

Material: 316 Stainless Steel

Approvals: CE

HITEMP140-TSK SPECIFICATIONS*

Operating Environment: -200 to +250°C (-328 to +482°F)
(Time limited)

0 to 100% RH

Dimensions: Flush Top: 2.75" x 2.0" dia.
(69.85mm x 51mm dia.)
Vented Top: 4.3" x 2.0" dia.
(109.2mm x 50.8mm dia.)

Material: Enclosure: PTFE

Weight: Flush Top: 8.2 oz. (232.5g)
(not including data logger)
Vented Top: 9.9 oz. (280.7g)
(not including data logger)

BATTERY WARNING: WARNING: FIRE, EXPLOSION, AND SEVERE BURN HAZARD. DO NOT SHORT CIRCUIT, CHARGE, FORCE OVER DISCHARGE, CRUSH, PENETRATE, OR INCINERATE. BATTERY MAY LEAK OR EXPLODE IF HEATED ABOVE 150°C (302°F).

*SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE. SPECIFIC WARRANTY REMEDY LIMITATIONS APPLY. CALL 1-603-456-2011 OR GO TO WWW.MADGETECH.COM FOR DETAILS.

**Other probe lengths up to 7" available. Contact MadgeTech for details.

Ambient Temperature	Exposure Time in Air	Exposure Time in Liquid
-200°C (-328°F)	18 minutes	N/A
-180°C (-292°F)	19 minutes	N/A
-160°C (-256°F)	21 minutes	N/A
-140°C (-220°F)	24 minutes	N/A
-120°C (-184°F)	27 minutes	N/A
-100°C (-148°F)	32 minutes	N/A
-80°C (-112°F)	40 minutes	N/A
-60°C (-76°F)	55 minutes	25 minutes
-40°C (-40°F)	70 minutes	32 minutes
-20°C to +140°C (-4°F to +284°F)	Indefinitely	Indefinitely
150°C (302°F)	88 minutes	40 minutes
160°C (320°F)	75 minutes	34 minutes
170°C (338°F)	63 minutes	29 minutes
180°C (356°F)	55 minutes	26 minutes
190°C (374°F)	50 minutes	23 minutes
200°C (392°F)	45 minutes	21 minutes
210°C (410°F)	42 minutes	19 minutes
220°C (428°F)	39 minutes	18 minutes
230°C (446°F)	36 minutes	17 minutes
240°C (464°F)	34 minutes	16 minutes
250°C (482°F)	32 minutes	15 minutes

ORDERING INFORMATION

MODEL	DESCRIPTION	PRICE (U.S.)	Enclosure
HITEMP140-2-TSK	HiTemp-2-140 data logger and thermal shield	\$549.00	Flush or Vented
HITEMP140-5-TSK	HiTemp-5-140 data logger and thermal shield	\$549.00	Flush or Vented
HITEMP140-7-TSK	HiTemp-7-140 data logger and thermal shield	\$549.00	Flush or Vented
IFC400	Docking station with USB cable, software and manual	\$120.00	
ER1425S-HT	Replacement battery for the HiTemp140-PT	\$50.00	
NIST	NIST Calibration Certificate	\$60.00	

ASK ABOUT
OUR OTHER
DATA
LOGGERS

Temperature
Humidity
Pressure
pH
Level
Shock
LCD Display
Pulse/Event/State
Current
Voltage
Wireless
Intrinsically Safe
Spectral Vibration
Motion

For Quantity Discounts call 603-456-2011 or email sales@madgetech.com

*To order the product with the NIST certificate add -CERT to the end of the part number and add \$60.00 to the price.



6 Warner Road · Warner, NH 03278
Phone: (603) 456-2011 · Fax: (603) 456-2012

DOC-1243009-00 REV 10